


SNMX-TZB-ALK

Hexalobular Socket Truss Head Screws with Nylon Patch



Vibration resistant treatment



Material/Finish




	SNMX-TZB-ALK
Main Body	Steel Trivalent Chromate Treatment
Nylon Patch	Nylon 11
Strength Class	4.8 Equivalent

Application

Screw return and fallout prevented
Prevention of damage to screw heads
Reliable tightening

Part Number Specification

SNMX-M5-20-TZB-ALK



- Hexalobular socket*1 truss machine screws with nylon patch.
- The friction of the nylon adhered to the thread suppresses the return rotation of the thread.
- Even if the tightening force is lost, the return rotation is suppressed, preventing the screws from falling off.
- The heat resistant temperature of the nylon patch is 120°C.
- Hexalobular socket shapes are designed to withstand high tightening torque compared to cross-recesses.
- Recesses are unlikely to be damaged due to tightening, allowing safe and secure tightening to be performed.

*1: The hexalobular shape is prescribed by JIS B 1015: 2008(ISO 10664: 2005)"Hexalobular internal driving feature for bolts and screws".

Unit : mm

Part Number	M (Coarse)		L								D1	L1	Hexalobular Socket No.	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch													
SNMX-M3-TZB-ALK	M3	0.5	6	8	10						6.9	1.9	10	0.63 - 0.79	10
SNMX-M4-TZB-ALK	M4	0.7	6	8	10	12	16	20	25	30	9.4	2.5	20	1.4 - 3.1	10
SNMX-M5-TZB-ALK	M5	0.8			10	12	16	20	25	30	11.8	3.1	25	2.8 - 5.5	10
SNMX-M6-TZB-ALK	M6	1			10	12	16				14	3.7	30	4.6 - 5.6	10

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

Related Products

SKX Hexalobular Wrench

SKX-N Hexalobular Wrench for Extremely Limited Access Spaces

SKXB Hexalobular Short Bit

SRD Magnet Screwdriver


Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available