




SFHS Flanged Hex Bolts

Easy operation **SUS** Stainless steel



Material/Finish



	SFHS
Main Body	SUS304
Strength Class	A2 - 50



- Stainless steel flanged hex bolts compliant with JIS B 1189.
- The head flange increases seating surface size, diffusing more pressure on the intended fastening material compared to conventional hex bolts and helping prevent seating surface sinking. Also, the seating surface can be ensured even for large drilled holes.
- Washer mounting work is not required, reducing the number of parts.
- Ideal for screw fastening automation using robots, as washers are not used.

Unit : mm

Part Number 1	M (Coarse)		L 2				D1	L1	B	t	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch										
SFHS-M6	M6	1	15	20	25	30	14	6	10	0.8	6.4 - 9	20
SFHS-M8	M8	1.25	15	20	25	30	17.5	8	12	1	12 - 17	10

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

Part Number Specification

SFHS-M6-25

1

2

1 Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Please feel free to contact us