





KMDFS-32-M6-HP
KMDFS-40-M8-HP

KMDFS-50-M10-HP
KMDFS-50-M12-HP



- Made of stainless steel superior in corrosion resistance.
- With an original design based on the 7 principles of universal design as well as ergonomics, force is easy to apply whether you hold it between your fingers or grasp with the palm of your hand, enabling stable operation. The shape is also designed for easy gripping with fingers, suitable for operation with work gloves on as well.
- The gently curved lines make the knob easy to wipe. With nowhere for water to puddle, it is also suitable for water washing.
- For applications requiring hygiene, such as food-related machinery, medical equipment, and chemical plants.

• Material/Finish



KMDFS	
Main Body	SCS13 (Equivalent to SUS304) Polishing

Unit : mm

Part Number	D	M (Coarse)		Lf min.	H	s	d	Mass (g)
		Nominal of Thread	Pitch					
KMDFS-32-M6-HP	32	M6	1	12	25	5	12	46
KMDFS-40-M8-HP	40	M8	1.25	15	30	5	16	94
KMDFS-50-M10-HP	50	M10	1.5	18	39	5	20	195
KMDFS-50-M12-HP	50	M12	1.75	18	39	5	20	190

• Part number specification

KMDFS-32-M6-HP

1

Cleanroom Wash & Packaging → P.0000	Screw Combination → P.0000	Screw Length Adjustment → P.0000	Vibration Resistant → P.0000	Laser Marking → P.0000
Please feel free to contact us	Please feel free to contact us	Not Available	Not Available	Not Available