



- Clamping screw with an integral special ball (full ball type).
- Point contact by full ball securely fixes a work.
- For tool holder set screw, pressure piece and stopper.
- We also produce products of special specifications, e.g. nominal diameter of thread, length and surface treatment. Please feel free to contact our customer service.

• Material/Finish



	SCSS-CE Ceramic Ball
Thread Part	Equivalent to SUS304
Ball	Alumina (Purity 99% or Above, Hardness 1100 HV)

Unit : mm

Part Number	M (Coarse)		L	D	B	Mass (g)
	Nominal of Thread	Pitch				
SCSS-M4-6-CE	M4	0.7	6.5	2.38	2	0.4
SCSS-M4-10-CE	M4	0.7	10.5	2.38	2	0.7
SCSS-M4-16-CE	M4	0.7	16.5	2.38	2	1
SCSS-M5-8-CE	M5	0.8	8.6	3.18	2.5	0.8
SCSS-M5-12-CE	M5	0.8	12.6	3.18	2.5	1.3
SCSS-M5-20-CE	M5	0.8	20.6	3.18	2.5	2.3
SCSS-M6-10-CE	M6	1	10.8	3.97	3	1.5
SCSS-M6-16-CE	M6	1	16.8	3.97	3	2.5
SCSS-M6-25-CE	M6	1	25.8	3.97	3	4
SCSS-M8-12-CE	M8	1.25	13.2	5.56	4	3.2
SCSS-M8-20-CE	M8	1.25	21.2	5.56	4	5.7
SCSS-M8-30-CE	M8	1.25	31.2	5.56	4	9
SCSS-M10-16-CE	M10	1.5	17.7	7.14	5	7
SCSS-M10-25-CE	M10	1.5	26.7	7.14	5	11
SCSS-M10-35-CE	M10	1.5	36.7	7.14	5	16
SCSS-M12-20-CE	M12	1.75	22	7.94	6	12.5
SCSS-M12-30-CE	M12	1.75	32	7.94	6	20
SCSS-M12-40-CE	M12	1.75	42	7.94	6	28

• Part Number Specification

SCSS-M4-16-CE



Cleanroom Wash & Packaging	Screw Combination	Screw Length Adjustment	Vibration Resistant
Please feel free to contact us	Available / Add'l charge	Not Available	Available / Add'l charge