



● 材質・仕上げ



	SM
本体	SUM22 クロムメッキ

単位：mm

品番 	D	M(並目)		Lm	d	H	h	h ₁	質量 (g)
		ねじの呼び	ピッチ						
SM-4	10	M4	0.7	9	7	32	28	4	10
SM-5	13	M5	0.8	10	8	40	35	5	25
SM-6	16	M6	1	13	10	50	43	7	45
SM-8	20	M8	1.25	15	13	64	56	8	90
SM-10	25	M10	1.5	18	16	80	70	10	180
SM-12	32	M12	1.75	20	20	100	87	13	350
SM-16	36	M16	2	22	22	112	98	14	500

- 品番指定 ※価格・納期はNBKウェブサイトをご覧ください。

SM-4



 クリーン洗浄・クリーン梱包 → P.xxxx 対応不可	 ゆるみ止め → P.xxxx 対応可・別料金	 レーザ刻印 → P.xxxx 対応不可	 軸穴追加工 → P.xxxx 対応不可
--	---	--	---