



- 両側めねじの六角支柱。

## ● 材質・仕上げ ①

RoHS

	SHB-EL スティール製 M(並目): M3, M4	SHB-EL スティール製 M(並目): M5-M8	SHBS ステンレス製
本体	SUM24L 無電解ニッケルメッキ	SUM22 無電解ニッケルメッキ	SUS304

## 寸法

単位: mm

品番 スティール製	品番 ステンレス製	M(並目)		B	C(約)	Lf1	Lf2	質量(g)
		ねじの呼び ②	ピッチ					
SHB-M3-EL	SHBS-M3	M3	0.5	6	6.9	6	6	2.9 - 9
SHB-M4-EL	SHBS-M4	M4	0.7	7	8.1	8	8	5 - 25
SHB-M5-EL	SHBS-M5	M5	0.8	8	9.2	10	10	5.5 - 40
SHB-M6-EL	SHBS-M6	M6	1	10	11.5	12	12	11 - 98
SHB-M8-EL	SHBS-M8	M8	1.25	13	15	16	16	27 - 168

## ねじ長さ

SHB-EL スティール製 SHBS ステンレス製

品番	L(mm) ③														
	15	20	25	30	35	40	45	50	60	70	80	90	100	120	150
SHB-M3-EL	●	●	●	●	●	●									
SHB-M4-EL		●	●	●	●	●	●	●	●	●	●				
SHB-M5-EL		●	●	●	●	●	●	●	●	●	●	●	●		
SHB-M6-EL			●	●	●	●	●	●	●	●	●	●	●	●	●
SHB-M8-EL					●	●	●	●	●	●	●	●	●	●	●
SHBS-M3	●	●	●	●	●	●									
SHBS-M4		●	●	●	●	●	●	●	●	●	●				
SHBS-M5		●	●	●	●	●	●	●	●	●	●	●	●		
SHBS-M6			●	●	●	●	●	●	●	●	●	●	●	●	●
SHBS-M8					●	●	●	●	●	●	●	●	●	●	●

- 品番指定 ※価格・納期はNBKウェブサイトをご覧ください。

## SHB-M4-40-EL



🧼 クリーン洗浄・クリーン梱包 → P.1640  
お問い合わせください

🔪 ねじカット → P.1644  
対応不可

🌀 ゆるみ止め → P.1645  
対応不可

🔪 レーザ刻印 → P.1656  
ステンレス製のみ対応可・別料金