



## ● 材質・仕上げ



	SCBS-R ステンレス製
ねじ部	SUS304相当
ボール	SUS440C (硬度 59 - 66HRC)

## ● 品番指定 ※価格・納期はNBKウェブサイトをご覧ください。

## SCBS-M6-20-R



単位: mm

品番 ステンレス製	M(並目)		L	D <sub>1</sub>	D	L <sub>1</sub>	B	許容荷重 (N)	質量 (g)
	ねじの呼び	ピッチ							
SCBS-M4-10-R	M4	0.7	10.5	7	2.5	4	3	2040	1.5
SCBS-M4-12-R	M4	0.7	12.5	7	2.5	4	3	2040	1.7
SCBS-M4-16-R	M4	0.7	16.5	7	2.5	4	3	2040	1.9
SCBS-M4-20-R	M4	0.7	20.5	7	2.5	4	3	2040	2.2
SCBS-M4-25-R	M4	0.7	25.5	7	2.5	4	3	2040	2.5
SCBS-M5-12-R	M5	0.8	12.6	8.5	3	5	4	3000	2.9
SCBS-M5-16-R	M5	0.8	16.6	8.5	3	5	4	3000	3.4
SCBS-M5-20-R	M5	0.8	20.6	8.5	3	5	4	3000	3.9
SCBS-M5-25-R	M5	0.8	25.6	8.5	3	5	4	3000	4.4
SCBS-M5-30-R	M5	0.8	30.6	8.5	3	5	4	3000	5
SCBS-M6-16-R	M6	1	16.8	10	4	6	5	4500	5.6
SCBS-M6-20-R	M6	1	20.8	10	4	6	5	4500	6.5
SCBS-M6-25-R	M6	1	25.8	10	4	6	5	4500	7.6
SCBS-M6-30-R	M6	1	30.8	10	4	6	5	4500	8.7
SCBS-M6-40-R	M6	1	40.8	10	4	6	5	4500	11
SCBS-M8-20-R	M8	1.25	21.2	13	5.56	8	6	9000	13.5
SCBS-M8-30-R	M8	1.25	31.2	13	5.56	8	6	9000	17.5
SCBS-M8-35-R	M8	1.25	36.2	13	5.56	8	6	9000	19
SCBS-M8-40-R	M8	1.25	41.2	13	5.56	8	6	9000	21.5
SCBS-M8-50-R	M8	1.25	51.2	13	5.56	8	6	9000	25
SCBS-M10-25-R	M10	1.5	26.7	16	7.14	10	8	14400	26
SCBS-M10-30-R	M10	1.5	31.7	16	7.14	10	8	14400	29
SCBS-M10-40-R	M10	1.5	41.7	16	7.14	10	8	14400	34
SCBS-M10-50-R	M10	1.5	51.7	16	7.14	10	8	14400	39
SCBS-M10-60-R	M10	1.5	61.7	16	7.14	10	8	14400	47
SCBS-M12-30-R	M12	1.75	32	18	7.94	12	10	18000	40
SCBS-M12-50-R	M12	1.75	52	18	7.94	12	10	18000	56
SCBS-M12-80-R	M12	1.75	82	18	7.94	12	10	18000	83
SCBS-M16-40-R	M16	2	43.3	24	11.91	16	14	43800	91
SCBS-M16-60-R	M16	2	63.3	24	11.91	16	14	43800	122
SCBS-M16-80-R	M16	2	83.3	24	11.91	16	14	43800	154

 クリーン洗浄・クリーン梱包  
お問い合わせください

 ねじ組み合わせ  
対応不可

 ねじカット  
対応不可

 ゆるみ止め  
対応可・別料金