




SFBS-UC

Socket Button Head Cap Screws with Flange for Sheet Metal

Protrusion Easy operation SUS Stainless steel



● Material/Finish



SFBS-UC

Main Body	SUSXM7 (Equivalent to SUS304)
Strength Class	A2-50

● Do not exceed the max. tightening torque.

● Application

Exterior panels on semiconductor manufacturing equipment, etc.
Reducing the size of equipment and devices


● Part Number Specification

SFBS-M5-10-UC


◀1 ▶2 ▶1

- These stainless steel socket button head cap screws with flange are for fixing thin plates.
- The flange on the head ensures a seating surface even on thin plates with large drilled holes, making fixing possible.
- Because **SFBS-UC** has relief in the under-head area, it is suitable for fixing thin plates. Fastening of thin plates from 0.1mm up is possible.

Standard socket button head cap screw with flange



Thin plate fixing socket button head cap screw with flange



- For space-saving of equipment/devices and applications with limited overhead space.
- Bolts for fixing thin plates are also available with special specifications such as dimensions, material, head shape, and so on. Please contact our customer service.



Unit : mm

Part Number	M (Coarse)		L	D1	D2	L1	t1	B	t	Max. Torque *1 (N·m)	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch										
SFBS-M3-UC	M3	0.5	4	5	6	8	7	5.2	1.65	0.5	2	1.05
SFBS-M4-UC	M4	0.7		5	6	8	9.2	6.8	2.2	0.6	2.5	1.3
SFBS-M5-UC	M5	0.8		6	8	10	11.4	8.5	2.75	0.8	3	1.6
SFBS-M6-UC	M6	1		6	8	10	13.6	10.1	3.3	0.9	4	2.1

*1 : Values in chart are for reference only. They are not guaranteed values.

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

Individual Sales Available / Add'l charge	Cleanroom Wash & Packaging Available / Add'l charge	Screw Length Adjustment Not Available	Vibration Resistant Available / Add'l charge	Modification process for captive use Not Available
--	--	--	---	---