



● Material/Finish



	SNZ3-TBZ
Main Body	Steel Black Trivalent Chromate Treatment



- Miniature screws for precision instruments (Type 0 - 3).
- M1.4 - M2.6.
- Pan head machine screw type with low head height. For applications with limited overhead space.

● Application

For making devices and equipment more compact
Compact precision equipment

Unit : mm

Part Number	M (Coarse)		L											D ₁	L ₁	Cross-recessed Socket No.	Max. Tightening Torque (N·m)*1	Mass (g)	Qty per Pack	
	Nominal of Thread	Pitch	1.5	2	2.5	3	3.5	4	5	6	8	10	12							
SNZ3-M1.4-TBZ	M1.4	0.3	1.5	2	2.5	3	3.5	4	5	6	8	10	12	2.5	0.8	0	0.07	0.04 - 0.12	50	
SNZ3-M1.6-TBZ	M1.6	0.35		2	2.5	3	3.5	4	5	6	8	10	12	2.8	0.85	0	0.11	0.05 - 0.16	50	
SNZ3-M1.7-TBZ	M1.7	0.35	1.5	2	2.5	3	3.5	4	5	6	8	10		3.0	0.9	0	0.14	0.06 - 0.16	50	
SNZ3-M2-TBZ	M2	0.4		2	2.5	3	3.5	4	5	6	8	10	12	3.5	1.0	0	0.22	0.09 - 0.27	50	
SNZ3-M2.5-TBZ	M2.5	0.45				3		4	5	6	8			4.3	1.3	0	0.46	0.2 - 0.34	50	
SNZ3-M2.6-TBZ	M2.6	0.45			2.5	3	3.5	4	5	6	8	10	12	14	4.5	1.2	0	0.53	0.19 - 0.55	50

*1 : Values in chart are for reference only. They are not guaranteed values.

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part Number Specification

SNZ3-M2-3-TBZ

1 2 1

Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Available / Add'l charge	Not Available