

- Dedicated cam base for mounting Quick Clamp Fasteners **NQTS-GL** **NQTS-NI-GL** **NQTS-F-GL** **NQTS-F-NI-GL** to sheet metal.
- The clamp part is tapered, making it easy to insert the Quick Clamp Fastener clamp pin.
- Made of stainless steel. It has excellent corrosion resistance.
- Uses low dust-emission grease.

⚠ Precautions for Use
If the grease deteriorates or runs low, apply grease (THK Co., Ltd.'s AFF Grease) to the sliding part.

• Material/Finish





	NQTBS-N-GL
Main Body	Equivalent to SUS630
Hex Nut	Equivalent to SUS304
Heat Resistance Temperature*1	100°C

*1: Upper limit temperature when using grease.

Part Number	D	L	M (Fine) Nominal of Thread	Pitch	L1	d1	d2	G	L2	B	T	C	Applicable Plate Thickness	Applicable Quick Clamp Fastener	Mass (g)
NQTBS-5-N-GL	25	16	M14	1.5	3	5	2	10.5	2	22	8	25.4	6~10	NQTS-5-GL NQTS-5-F-GL NQTS-5-NI-GL NQTS-5-F-NI-GL	37
NQTBS-8-N-GL	32	18	M20	1.5	3	8	2	13	2	30	10	34.6	6~12	NQTS-8-GL NQTS-8-L-GL NQTS-8-F-GL NQTS-8-NI-GL NQTS-8-L-NI-GL NQTS-8-F-NI-GL	69

Unit : mm

- Mounting
Align the phase of the Quick Clamp Fastener **NQTS-GL** **NQTS-NI-GL** **NQTS-F-GL** **NQTS-F-NI-GL** clamp pin and the **NQTBS-N-GL** pin mounting hole for mounting.
The **NQTBS-N-GL** pin mounting hole orientation is determined by the pin hole machining position in the mounting plate side.



Part Number	D	d4	h	G	Lc	d3
NQTBS-5-N-GL	25	15	3.5	10.5	3	2.2
NQTBS-8-N-GL	32	21	3.5	13	3	2.2

Unit : mm

• Part Number Specification

NQTBS-8-N-GL

