

● Material/Finish



	NQTS-NI-GF
Main Body	SUS303
Knob	Equivalent to SUS304
Hex Socket Head Cap Screw	Stainless Steel
Heat Resistance Temperature*1	100°C

*1: Upper limit temperature when using grease.

- In combination with the dedicated cam base, jigs can be easily mounted and removed without tools.
- Just rotate the knob 90° to clamp and unclamp: ideal for repetitive work.
- The knob is reverse-tapered to a hand-friendly round shape, with laser engraving on the main body enabling corrosion resistance to be retained.
- The knob projection and laser engraving make the clamping status clear at a glance.
- The knob operation part has passed 50,000 operation tests. With excellent endurance, it reduces part replacement frequency.
- Made of all stainless steel.
- Uses NSF H1 registered grease. Suitable for use in food machinery.
- Two hex socket head cap screws for mounting are provided.
- For mounting to plates from 3mm to less than 6mm, use the dedicated spacer **NQTS-SPCR**.



Precautions for Use


Scarce or deteriorating grease may increase operating force. In this case, apply grease (NOK Klüber's Klübersynth UH1 14 - 222) to the dedicated cam base sliding part.

Unit : mm

Part Number	F	L1	L3	L	L2	D	M (Coarse)		Lf	E	B	L4	Applicable Plate Thickness		Repeated Positioning Accuracy	Clamping Force*1 (N)	Mass (g)
							Nominal of Thread	Pitch					Without NQTS-SPCR	With NQTS-SPCR			
NQTS-5-NI-GF	25	22	5.5	14	6.5	13.9	M2.5	0.45	4	10	5	15.1	6~10	3~6	±0.1	60	56
NQTS-8-NI-GF	34	28	5.5	18	10	18.5	M3	0.5	6	13	8	16.5	6~14	3~6	±0.1	90	135
NQTS-8-L-NI-GF	34	28	5.5	18	10	18.5	M3	0.5	6	13	8	22.5	12~20	-	±0.1	90	137

*1: Clamping force is the maximum allowable load retaining the mounting plate clearance within 0.1mm against tensile load.

● Max. Allowable Load




Part Number	Max. Allowable Shear Load (N)	Max. Allowable Tensile Load (N)
NQTS-5-NI-GF	1800	1200
NQTS-8-NI-GF	3200	2600
NQTS-8-L-NI-GF	3200	2600



● Usage Example

In combination with dedicated cam base **NQTBS-GF**, etc.



● Related Products

Dedicated cam bases are available.



Dedicated spacer **NQTS-SPCR** is available.



● Part Number Specification


NQTS-8-L-NI-GF



● Mounting


The LOCK display is laser engraved on a straight line from the mounting hole. Set the LOCK display and mounting hole position with attention to workability.

When the plate thickness is from 3mm to less than 6mm, refer to **NQTS-SPCR** mounting.



Part Number	Applicable Plate Thickness	l	h	E	d	d ₁	h ₁
NQTS-5-NI-GF	6	14	6	10	2.9	5.5	2.5
NQTS-8-NI-GF	6	18	6	13	3.4	6.5	2.5
NQTS-8-L-NI-GF	12	18	12	13	3.4	6.5	2.5

Unit : mm




Part Number	Applicable Plate Thickness	l	D ₁	h	E	d	d ₁	h ₁
NQTS-5-NI-GF	6 - 10	14	26	6	10	2.9	5.5	2.5
NQTS-8-NI-GF	6 - 14	18	35	6	13	3.4	6.5	2.5
NQTS-8-L-NI-GF	12 - 20	18	35	12	13	3.4	6.5	2.5

Unit : mm

● Pitch Precision Between Holes

The pitch tolerance of the **NQTS-NI-GF** mounting plate and the cam base mounting plate should be ± 0.04mm or below.



● Repeated Positioning Accuracy

Repeated positioning accuracy is ±0.1mm. When even higher-precision positioning is required, prepare a positioning pin suited to the application.

