

● Material/Finish




	NQTS-HP
Main Body	SUS630

Part Number	L1	L2	D	M (Coarse)		D1	B	t	Applicable Quick Clamp Fastener	Mass (g)
				Nominal of Thread	Pitch					
NQTS-6-HP	7.6	5.8	5.5	M4	0.7	6	2.5	1.3	NQTS-6-PH-BK NQTS-6-PH-NI	2
NQTS-8-HP	8.7	5.8	6.5	M5	0.8	8	2.5	1.3	NQTS-8-PH-BK NQTS-8-PH-NI	3

- Dedicated holding pin for Quick Clamp Fasteners **NQTS-PH** **NQTS-PH-NI**.
- Made of stainless steel. It has excellent corrosion resistance.




- Mounting
- When Mounting on a Flat Surface



Part Number	M (Coarse)	
	Nominal of Thread	Pitch
NQTS-6-HP	M4	0.7
NQTS-8-HP	M5	0.8

- When $I > E$
I: Quick Clamp Fastener fitting part diameter
E: Holding pin mounting part outside diameter
Make a spot facing hole to achieve the retention force as indicated in the specifications.



Part Number	M (Coarse)		D2	h	Lf min.	E max.	I
	Nominal of Thread	Pitch					
NQTS-6-HP	M4	0.7	7	0.5	6	14	14
NQTS-8-HP	M5	0.8	9	0.5	6	18	18

- Part Number Specification

NQTS-6-HP

