

Service description

- Scale plates and scale stickers will be cut in 1 mm to your desired length.
- This service makes it easier to use scale plates and scale stickers according to spaces or purposes of equipment or devices.



Applicable Products

FSP Scale plates (Horizontal types)

FSP-V Scale plates (Vertical types)

FSS **FST** Scale Stickers (Horizontal types)

FSS-V **FST-V** Scale stickers (Vertical types)

Fees • Delivery

- Please feel free to contact us.

Part number specification

FSP-100-L-CT-L 10-R 10


Product part number




Please specify end face to be cut and cutting position (unit: 1 mm) by adding **-CT** to the end of the product part number.

Order placement flow

- ① Select processing symbol **CT**. ◀ 1
 - ② Select end face to be cut. ◀ 2
 - Horizontal types **FSP** **FSS** **FST**
 - Left side cutting: **L**
 - Right side cutting: **R**
 - Vertical types **FSP-V** **FSS-V** **FST-V**
 - Upper part cutting: **T**
 - Lower part cutting: **B**
 - ③ Please specify the cutting position from scale on the end face to be cut in the unit of 1 mm. ◀ 3
- Example: One-side cutting
FSP-100-L (scale length: 100 mm) is cut at a position of 15 mm from left end scale, part number will be **FSP-100-L-CT-L15**.



- Example: Two-side cutting
FSP-100-L (scale length: 100 mm) is cut at a position of 15 mm from left end scale and 10 mm from right end scale, part number will be **FSP-100-L-CT-L15-R10**.



- To leave scale on the cut face, neither R processing nor C-face processing on the cut face will be performed.
- Tolerance of the cutting position is ± 0.5 mm.
- As for two-side cutting, specify the cutting position from left side in the case of horizontal types, and from upside in the case of vertical types.