




SNSS-J Socket Head Cap Screws

SUS Stainless steel



- Conforms to JIS B 1176, ISO 4762, and DIN 912.
⇒ Technical Information : JIS B 1176, ISO 4762
- M3 - M16. Selection from abundant size variations is available to suit the device or equipment.
- Captive Processing Service is supported for M10 and M12.
- M3 to M8 captive-processed hex socket head cap screws **SSC** are available.

- Material/Finish



	SNSS-J
Main Body	SUSXM7 (Equivalent to SUS304)
Strength Class	A2-70

Unit : mm

Part Number 	M (Coarse)		L 													D1	L1	B	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch	4	5	6	8	10	12	16	20										
SNSS-M3	M3	0.5														5.5	3	2.5	0.63 - 1.4	20
SNSS-M4	M4	0.7														7	4	3	1.4 - 3.2	20
SNSS-M5	M5	0.8														8.5	5	4	2.2 - 4.8	20
SNSS-M6	M6	1														10	6	5	4.3 - 8.3	20
SNSS-M8	M8	1.25														13	8	6	10 - 19	10
SNSS-M10	M10	1.5														16	10	8	21 - 33	5
SNSS-M12	M12	1.75														18	12	10	39 - 55	1
SNSS-M16	M16	2														24	16	14	91 - 122	1

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

- Part Number Specification

SNSS-M5 - 12



 Individual Sales	 Cleanroom Wash & Packaging	 Screw Length Adjustment	 Vibration Resistant	 Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Please feel free to contact us