



● Material/Finish



	SNZB
Main Body	Brass*1

*1: The coloring may change over time or in response to environmental conditions, but the performance will not be affected.



- Miniature screws for precision instruments (Type 0 - 1).
- M2/M2.6.
- Pan head machine screw type with low head height. For applications with limited overhead space.
- Non-magnetic.
- Application

For making devices and equipment more compact
FPD production equipment / Semiconductor manufacturing equipment / Electronic equipment / Miniature precision devices

Unit : mm

Part Number 1	M (Coarse)		L 2								D1	L1	Cross-recessed Socket No.	Max. Tightening Torque (N·m)*1	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch	2	3	4	5	6	7	8	9						
SNZB-M2	M2	0.4									3	0.6	0	0.18	0.08 - 0.14	50
SNZB-M2.6	M2.6	0.45								10	4	0.8	0	0.23	0.2 - 0.4	50

*1: Values in chart are for reference only. They are not guaranteed values.

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part Number Specification

SNZB-M2-3

1
2

Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Not Available