




SNF-TBZ-SUC-ALK

Cross Recessed Flat Head Machine Screws with Nylon Patch - for Sheet Metal

Protrusion Vibration resistant treatment




● Material/Finish

	SNF-TBZ-SUC-ALK	RoHS
Main Body	SWCH12A Black Trivalent Chromate Treatment	
Nylon Patch	Nylon 11	

- Phillips cross recessed flat head machine screws with cut bearing surface.
- With nylon patch.
- Suitable for sheet metal fixing, preventing bearing surfaces and incomplete thread parts from hitting the bottom during fixing.

Standard flat head machine screw SNF-TBZ-SUC-ALK



- Incomplete thread part of no more than 2 screw threads or so.
- The friction of the nylon adhered to the thread suppresses the return rotation of the thread.
- Even if the tightening force is lost, the return rotation is suppressed, preventing the screws from falling off.
- The heat resistant temperature of the nylon patch is 120°C.

● Application

Reducing the size of equipment and devices
Screw return and fallout prevented

Unit : mm

Part Number	M (Coarse)		L	D1	L1	Cross-recessed Socket No.	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch						
SNF-M3-TBZ-SUC-ALK	M3	0.5	4 5 6 8 10	6	1.2	1	0.3 - 0.46	50
SNF-M4-TBZ-SUC-ALK	M4	0.7	4 5 6 8 10 12 15	8	1.5	2	0.3 - 1.2	50
SNF-M5-TBZ-SUC-ALK	M5	0.8	5 6 8 10 12 15 10	2	2		1.3 - 2.1	20
SNF-M6-TBZ-SUC-ALK	M6	1	6 8 10 12 15 12	2.3	2		1.7 - 3.4	20

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part Number Specification

SNF-M5-12-TBZ-SUC-ALK

Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available