

SNZ2S-ALK

Cross Recessed Micro Pan Head Screws with Nylon Patch - Type 0 - 2




Vibration resistant treatment



Miniature Size



SUS Stainless steel



- Material/Finish



RoHS

| | SNZ2S-ALK |
|-------------|------------------|
| Main Body | Stainless Steel |
| Nylon Patch | Nylon 11 |





- Miniature screws with nylon patch for precision instruments (No. 0 Class 2).
- M1.4 - M2.
- The friction of the nylon adhered to the thread suppresses the return rotation of the thread.
- Even if the tightening force is lost, the return rotation is suppressed, preventing the screws from falling off.
- The heat resistant temperature of the nylon patch is 120°C.
- Pan head machine screw type with low head height. For applications with limited overhead space.

- Application

Screw return and fallout prevented
For making devices and equipment more compact
Compact precision equipment

Unit : mm

| Part Number  | M (Coarse) | | L  | | | | | | | | | | D1 | L1 | Cross-recessed Socket No. | Max. Tightening Torque (N·m) | Mass (g) | Qty per Pack |
|---|-------------------|-------|---|-----|---|-----|---|---|---|---|----|----|-----|------|---------------------------|------------------------------|-------------|--------------|
| | Nominal of Thread | Pitch | | | | | | | | | | | | | | | | |
| SNZ2S-M1.4-ALK | M1.4 | 0.3 | 2 | 2.5 | 3 | 3.5 | 4 | 5 | 6 | 8 | 10 | | 2.5 | 0.5 | 0 | 0.03 | 0.03 - 0.1 | 50 |
| SNZ2S-M1.6-ALK | M1.6 | 0.35 | 2 | 2.5 | 3 | 3.5 | 4 | 5 | 6 | 8 | 10 | | 2.8 | 0.55 | 0 | 0.05 | 0.04 - 0.12 | 50 |
| SNZ2S-M1.7-ALK | M1.7 | 0.35 | 2 | | 3 | 3.5 | 4 | 5 | | 8 | 10 | | 3.0 | 0.5 | 0 | 0.07 | 0.05 - 0.14 | 50 |
| SNZ2S-M2-ALK | M2 | 0.4 | 2 | 2.5 | 3 | 3.5 | 4 | 5 | 6 | 8 | 10 | 12 | 3.5 | 0.6 | 0 | 0.12 | 0.07 - 0.21 | 50 |

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

- Part Number Specification

SNZ2S-M2-3-ALK**1** Individual Sales

Available / Add'l charge

Cleanroom Wash & Packaging

Available / Add'l charge

Screw Length Adjustment

Not Available

Vibration Resistant

Not Available

Modification process for captive use

Not Available