

SNZ3-TZB-ALK


Cross Recessed Micro Pan Head Machine Screws with Nylon Patch - Type 0 - 3



Vibration resistant treatment



Miniature Size



● Material/Finish



RoHS

	SNZ3-TZB-ALK
Main Body	Steel Trivalent Chromate Treatment
Nylon Patch	Nylon 11



- Miniature screws with nylon patch for precision instruments (Type 0 - 3).
- M1.4 - M2.6.
- Pan head machine screw type with low head height. For applications with limited overhead space.
- The friction of the nylon adhered to the thread suppresses the return rotation of the thread.
- Even if the tightening force is lost, the return rotation is suppressed, preventing the screws from falling off.
- The heat resistant temperature of the nylon patch is 120°C.

● Application

For making devices and equipment more compact
Screw return and fallout prevented
Compact precision equipment

Unit : mm

Part Number 	M (Coarse)		L 	D1	L1	Cross-recessed Socket No.	Max. Tightening Torque (N·m)*1	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch							
SNZ3-M1.4-TZB-ALK	M1.4	0.3	2 2.5 3 3.5 4 5 6 8 10 12	2.5	0.8	0	0.05	0.04 - 0.12	50
SNZ3-M1.6-TZB-ALK	M1.6	0.35	2 2.5 3 3.5 4 5 6 8 10 12	2.8	0.85	0	0.07	0.05 - 0.16	50
SNZ3-M1.7-TZB-ALK	M1.7	0.35	2 2.5 3 3.5 4 5 6 8 10	3.0	0.9	0	0.09	0.06 - 0.16	50
SNZ3-M2-TZB-ALK	M2	0.4	2 2.5 3 3.5 4 5 6 8 10 12 14	3.5	1.0	0	0.18	0.09 - 0.31	50
SNZ3-M2.5-TZB-ALK	M2.5	0.45	3 4 5 6 8	4.3	1.3	0	0.32	0.2 - 0.34	50
SNZ3-M2.6-TZB-ALK	M2.6	0.45	2.5 3 3.5 4 5 6 8 10 12 14	4.5	1.2	0	0.39	0.19 - 0.55	50

*1 : Values in chart are for reference only. They are not guaranteed values.

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part Number Specification

SNZ3-M2 - 3 - TZB-ALK

 Individual Sales	 Cleanroom Wash & Packaging	 Screw Length Adjustment	 Vibration Resistant	 Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available