

**SNZ3-TBZ-ALK**


Cross Recessed Micro Pan Head Machine Screws with Nylon Patch - Type 0 - 3



Vibration resistant treatment



Miniature Size



- Material/Finish





	<b>SNZ3-TBZ-ALK</b>
Main Body	Steel Black Trivalent Chromate Treatment
Nylon Patch	Nylon 11



- Miniature screws with nylon patch for precision instruments (Type 0 - 3).
- M1.4 - M2.6.
- Pan head machine screw type with low head height. For applications with limited overhead space.
- The friction of the nylon adhered to the thread suppresses the return rotation of the thread.
- Even if the tightening force is lost, the return rotation is suppressed, preventing the screws from falling off.
- The heat resistant temperature of the nylon patch is 120°C.
- Application

For making devices and equipment more compact  
Screw return and fallout prevented  
Compact precision equipment

Unit : mm

Part Number 	M (Coarse)		L 										D1	L1	Cross-recessed Socket No.	Max. Tightening Torque (N · m)*1	Mass (g)	Qty per Pack	
	Nominal of Thread	Pitch																	
SNZ3-M1.4-TBZ-ALK	M1.4	0.3	2	2.5	3	3.5	4	5	6	8	10	12	2.5	0.8	0	0.05	0.04 - 0.12	50	
SNZ3-M1.6-TBZ-ALK	M1.6	0.35	2	2.5	3	3.5	4	5	6	8	10	12	2.8	0.85	0	0.07	0.05 - 0.16	50	
SNZ3-M1.7-TBZ-ALK	M1.7	0.35	2	2.5	3	3.5	4	5	6	8	10		3.0	0.9	0	0.09	0.06 - 0.16	50	
SNZ3-M2-TBZ-ALK	M2	0.4	2	2.5	3	3.5	4	5	6	8	10	12	3.5	1.0	0	0.18	0.09 - 0.27	50	
SNZ3-M2.5-TBZ-ALK	M2.5	0.45			3			4	5	6	8		4.3	1.3	0	0.32	0.2 - 0.34	50	
SNZ3-M2.6-TBZ-ALK	M2.6	0.45		2.5	3	3.5	4	5	6	8	10	12	14	4.5	1.2	0	0.39	0.19 - 0.55	50

\*1 : Values in chart are for reference only. They are not guaranteed values.

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

- Part Number Specification

**SNZ3-M2 - 3 - TBZ-ALK**

<b>1</b> Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available