




Vibration resistant treatment



Miniature Size



SUS Stainless steel



• Material/Finish



RoHS



	SNZ3S-ALK
Main Body	Stainless Steel
Nylon Patch	Nylon 11



- Miniature screws with nylon patch for precision instruments (Type 0 - 3).
- M1.4 - M2.6.
- Pan head machine screw type with low head height. For applications with limited overhead space.
- The friction of the nylon adhered to the thread suppresses the return rotation of the thread.
- Even if the tightening force is lost, the return rotation is suppressed, preventing the screws from falling off.
- The heat resistant temperature of the nylon patch is 120°C.
- Application

For making devices and equipment more compact
Screw return and fallout prevented
Compact precision equipment

Unit : mm

Part Number 	M (Coarse)		L 	D1	L1	Cross-recessed Socket No.	Max. Tightening Torque (N·m)*1	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch							
SNZ3S-M1.4-ALK	M1.4	0.3	2 2.5 3 3.5 4 5 6 8 10 12	2.5	0.8	0	0.03	0.04 - 0.13	50
SNZ3S-M1.6-ALK	M1.6	0.35	2 2.5 3 3.5 4 5 6 8 10	2.8	0.85	0	0.05	0.05 - 0.14	50
SNZ3S-M1.7-ALK	M1.7	0.35	2 2.5 3 3.5 4 5 6 8 10 12 14	3.0	0.9	0	0.07	0.06 - 0.18	50
SNZ3S-M2-ALK	M2	0.4	2 2.5 3 3.5 4 5 6 8 10 12 14	3.5	1.0	0	0.12	0.09 - 0.3	50
SNZ3S-M2.6-ALK	M2.6	0.45	3 4 6 8	4.5	1.2	0	0.28	0.21 - 0.36	50


*1 : Values in chart are for reference only. They are not guaranteed values.

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

• Part Number Specification

SNZ3S-M2-3-ALK



 Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available