

SNZF-TZB-ALK


Cross Recessed Micro Flat Head Machine Screws with Nylon Patch - Type 0 - 1



Vibration resistant treatment



Miniature Size



● Material/Finish



RoHS

	SNZF-TZB-ALK
Main Body	Steel Trivalent Chromate Treatment
Nylon Patch	Nylon 11

- Miniature screws with nylon patch for precision instruments (Type 0 - 1).
- M1.4 - M2.6.
- Head is more compact than standard flat head machine screws.
- The friction of the nylon adhered to the thread suppresses the return rotation of the thread.
- Even if the tightening force is lost, the return rotation is suppressed, preventing the screws from falling off.
- The heat resistant temperature of the nylon patch is 120°C.

● Application

For making devices and equipment more compact
Screw return and fallout prevented
Compact precision equipment

Unit : mm

Part Number ◀1	M (Coarse)		L ▶2	D1	L1	Cross-recessed Socket No.	Max. Tightening Torque (N·m)*1	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch							
SNZF-M1.4-TZB-ALK	M1.4	0.3	2.5 3 3.5 4 5 6 8 10	2.0	0.45	0	0.05	0.02 - 0.08	50
SNZF-M1.6-TZB-ALK	M1.6	0.35	2.5 3 3.5 4 5 6 8	2.4	0.5	0	0.07	0.03 - 0.09	50
SNZF-M1.7-TZB-ALK	M1.7	0.35	2.5 3 3.5 4 5 6 8 10	2.5	0.5	0	0.09	0.04 - 0.13	50
SNZF-M2-TZB-ALK	M2	0.4	3 3.5 4 5 6 8 10	3.0	0.6	0	0.18	0.06 - 0.18	50
SNZF-M2.5-TZB-ALK	M2.5	0.45	3 4 5 6	3.8	0.8	0	0.32	0.1 - 0.19	50
SNZF-M2.6-TZB-ALK	M2.6	0.45	3 4 5 6 8 10	4.0	0.8	0	0.39	0.12 - 0.33	50

*1 : Values in chart are for reference only. They are not guaranteed values.

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part Number Specification

SNZF-M2-3-TZB-ALK

◀1

▶2

◀1

1 Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available