




# SPC-SW Plastic Captive Washers - PC

Lightweight Electrical Insulation



- PC (polycarbonate) retaining washers for small screws.
- PC (polycarbonate) has the highest shock resistance of engineering plastics.
- Allowable operating temperature\*1 (min./max.): -40°C/115°C
- PC has low water absorbency and excellent weather resistance.
- For the properties and precautions for use of plastic screws, see "Properties of Plastic Screws."

## Application

Electrical and electronic equipment

## Material/Finish



	SPC-SW
Main Body	PC (Polycarbonate) (Transparent)
Heat Resistance Temperature*1	115°C

\*1: This is the value for the resin material. The operating temperature of the product changes with performance conditions such as tightening torque.

Unit : mm

Part Number	d	D	t	Nominal	Mass (g)	Qty per Pack
SPC-3-SW	2.8	8	0.5	3	0.03	100
SPC-3-SW(1000)	2.8	8	0.5	3	0.03	1000
SPC-4-SW	3.65	10	0.8	4	0.05	100
SPC-4-SW(5000)	3.65	10	0.8	4	0.05	5000
SPC-5-SW	4.6	12	0.8	5	0.07	100
SPC-5-SW(2500)	4.6	12	0.8	5	0.07	2500
SPC-6-SW	5.5	13	1	6	0.13	100
SPC-6-SW(2500)	5.5	13	1	6	0.13	2500

• When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

## Part Number Specification

### SPC-4-SW



Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available