



● Material/Finish



	SNMXS-ALK
Material	SUSXM7 (Equivalent to SUS304)
Nylon Patch	Nylon 11

● Application

Screw return and fallout prevented
Prevention of damage to screw heads
Reliable tightening

● Part Number Specification

SNMXS-M5-20-ALK

1

2

1



- Hexalobular socket*1 truss machine screws with nylon patch.
- The friction of the nylon adhered to the thread suppresses the return rotation of the thread.
- Even if the tightening force is lost, the return rotation is suppressed, preventing the screws from falling off.
- The heat resistant temperature of the nylon patch is 120°C.
- Hexalobular socket shapes are designed to withstand high tightening torque compared to cross-recesses.
- Recesses are unlikely to be damaged due to tightening, allowing safe and secure tightening to be performed.

*1 : The hexalobular shape is prescribed by JIS B 1015: 2008(ISO 10664: 2005)"Hexalobular internal driving feature for bolts and screws".

Unit : mm

Part Number 1	M (Coarse)		L 2								D1	L1	Hexalobular Socket No.	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch													
SNMXS-M3-ALK	M3	0.5	6	8	10	12					6.9	1.9	10	0.58 - 0.82	10
SNMXS-M4-ALK	M4	0.7	6	8	10	12	16	20			9.4	2.5	20	1.4 - 2.5	10
SNMXS-M5-ALK	M5	0.8		8	10	12	16	20			11.8	3.1	25	2.9 - 4.3	10
SNMXS-M6-ALK	M6	1			10	12	16	20	25	30	14	3.7	30	5.2 - 8.7	10
SNMXS-M8-ALK	M8	1.25					16	20	25	30	17.8	4.8	40	13 - 17	10

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Related Products

SKX Hexalobular Wrench



SKXB Hexalobular Short Bit



SKX-N Hexalobular Wrench for Extremely Limited Access Spaces



SRD Magnet Screwdriver



1 Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available