




# SPA-Z(INCH) Plastic Inch Threaded Rods - RENY

Lightweight High Specific Strength



## Material/Finish



SPA-Z(INCH)	
Main Body	RENY™*1 (50% Glass Fiber Reinforced Polyamide MXD6) (Ivory)
Heat Resistance Temperature*2	105℃

\*1: RENY™ is a trademark or registered trademark of Mitsubishi Gas Chemical Company, Inc.

\*2: This is the value for the resin material. The operating temperature of the product changes with performance conditions such as tightening torque.

- RENY™ threaded rods.
- Inch screw type.
- RENY™ is a thermoplastic engineering plastic with excellent tensile and bending strength.
- It is highly fatigue-resistant and has excellent creep and heat insulation properties.
- While it is nearly as strong as metal, its weight is approximately 1/5 of iron.
- For the properties and precautions for use of plastic screws, see "Properties of Plastic Screws."

## Application

Heat insulation and dew condensation prevention of refrigerating and freezing facilities  
Electrical and electronic equipment / Offshore instruments / Plating facilities

Unit : mm

Part Number 	W (Whitworth)		L	Mass (g)
	Nominal of Thread	Pitch		
<b>SPA-W3 / 8-Z</b>	W3/8	1.5875	300	32.6

## Part Number Specification

### SPA-W3/8-Z



Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
1 piece in 1 pack	Available / Add'l charge	Not Available	Not Available	Not Available