



● Material/Finish



	<b>KP</b>
knob	Nylon 6 (Black)
Thread Part	SS400 Trivalent Chromate Treatment

Unit : mm

Part Number	D	M (Coarse)		Lm	H	s	d	Mass (g)
		Nominal of Thread	Pitch					
<b>KP-30A</b>	30	M6	1	30	10	3	15	12
<b>KP-30</b>	30	M8	1.25	30	10	3	15	17
<b>KP-50</b>	50	M10	1.5	40	16	2	20	49
<b>KP-65</b>	65	M10	1.5	50	18	2	23	66
<b>KP-65B</b>	65	M12	1.75	50	18	2	23	83

● Part number specification

**KP-50**



Cleanroom Wash & Packaging → P.xxxx	Screw Combination → P.xxxx	Screw Length Adjustment → P.xxxx	Vibration Resistant → P.xxxx	Laser Marking → P.xxxx
Not Available	Not Available	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge