




# SEQ-TBZ-ALK

Super Ultra Low Profile Cross Recessed Machine Screws with Nylon Patch

Protrusion

Vibration resistant treatment



## ● Material/Finish

SEQ-TBZ-ALK	
Main Body	SWCH Black Trivalent Chromate Treatment
Nylon Patch	Nylon 11



- Cross recessed head cap screws with extra low profile.
- With nylon patch.
- For space-saving of equipment/devices and applications with limited overhead space.
- QuaStix<sup>\*1</sup> is used for the cross recess. By using a dedicated bit for QuaStix **SKQB**, the torque transmission is improved, preventing cam-out and damage to the cross recess.\*<sup>2</sup>
- The friction of the nylon adhered to the thread suppresses the return rotation of the thread.
- Even if the tightening force is lost, the return rotation is suppressed, preventing the screws from falling off.
- The heat resistant temperature of the nylon patch is 120°C.

\*1: QuaStix is a registered trademark of OSG Corporation.

\*2: It can be mounted and removed with ordinary Phillips bits.

## ● Application

Reducing the size of equipment and devices  
Screw return and fallout prevented

Unit : mm

Part Number <b>①</b>	M (Coarse)		L <b>②</b>	D1	L1	Bit Part No.	Max. Tightening Torque (N·m)* <sup>1</sup>	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch							
SEQ-M3-TBZ-ALK	M3	0.5	6 8 10 12	7	0.8	SKQB-1	0.6	0.39 - 0.64	10
SEQ-M4-TBZ-ALK	M4	0.7	8 10 12 16	8	0.9	SKQB-2	1.2	0.8 - 1.4	10

\*1: Values in chart are for reference only. They are not guaranteed values.

\*2: When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

## ● Related Products

Use dedicated bit **SKQB** for mounting and removing.

## ● Part Number Specification

**SEQ-M3-8-TBZ-ALK****① ② ①****1** Individual Sales

Available / Add'l charge

**2** Cleanroom Wash & Packaging

Available / Add'l charge

**3** Screw Length Adjustment

Not Available

**4** Vibration Resistant

Not Available

**5** Modification process for captive use

Not Available