




SNMS-UC Truss Head Phillips Screws for Sheet Metal

Protrusion Easy operation SUS Stainless steel



● Material/Finish

	SNMS-UC	RoHS
Main Body	SUSXM7 (Equivalent to SUS304)	
Strength Class	A2-50	

● Application

Exterior panels on semiconductor manufacturing equipment, etc.
Reducing the size of equipment and devices


● Part Number Specification

SNMS-M5-10-UC

1 2 1



- These stainless steel cross recessed truss machine screws are for fixing thin plates.
- The large head ensures a seating surface even on thin plates with large drilled holes, making fixing possible.
- Because **SNMS-UC** has relief in the under-head area, it is suitable for fixing thin plates. Fastening of thin plates from 0.1mm up is possible.



- For space-saving of equipment/devices and applications with limited overhead space.
- Bolts for fixing thin plates are also available with special specifications such as dimensions, material, head shape, and so on. Please contact our customer service.



Part Number	M (Coarse)		L	2	D1	L1	Cross-recessed Socket No.	Mass (g)	Qty per Pack	Unit : mm	
	Nominal of Thread	Pitch									
SNMS-M3-UC	M3	0.5	4	5	6	8	6.9	1.9	1	0.79 - 1	10
SNMS-M4-UC	M4	0.7		5	6	8	9.4	2.5	2	1.9 - 2.2	10
SNMS-M5-UC	M5	0.8			6	8	11.8	3.1	2	3.6 - 4.2	10
SNMS-M6-UC	M6	1			6	8	10	14	3.7	5.9 - 6.8	10

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Available / Add'l charge	Not Available