




SNMX-TBZ Hexalobular Socket Truss Head Screws



Material/Finish



	SNMX-TBZ
Main Body	Steel Black Trivalent Chromate Treatment
Strength Class	4.8 Equivalent


- Hexalobular socket shapes*1 are designed to withstand high tightening torque compared to cross-recesses.
- Recesses are unlikely to be damaged due to tightening, allowing safe and secure tightening to be performed.

*1: The hexalobular shape is prescribed by JIS B 1015: 2008(ISO 10664: 2005) "Hexalobular internal driving feature for bolts and screws".

Application

Prevention of damage to screw heads
Reliable tightening

Unit : mm

Part Number 	M (Coarse)		L 						D1	L1	Hexalobular Socket No.	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch											
SNMX-M3-TBZ	M3	0.5	6	8	10				6.9	1.9	10	0.63 - 0.79	20
SNMX-M4-TBZ	M4	0.7	6	8	10	12	16	20	9.4	2.5	20	1.4 - 2.3	20
SNMX-M5-TBZ	M5	0.8			10	12	16	20	11.8	3.1	25	2.7 - 3.1	20
SNMX-M6-TBZ	M6	1			10	12	16		14	3.7	30	3.6 - 4.9	20

• When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

Related Products

SKX Hexalobular Wrench



SKX-N Hexalobular Wrench for Extremely Limited Access Spaces



SKXB Hexalobular Short Bit








SRD Magnet Screwdriver



Part Number Specification

SNMX-M5-20-TBZ

 Individual Sales	 Cleanroom Wash & Packaging	 Screw Length Adjustment	 Vibration Resistant	 Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Not Available