




SEQ-TZB-ALK

Super Ultra Low Profile Cross Recessed Machine Screws with Nylon Patch

Protrusion

Vibration resistant treatment



● Material/Finish

SEQ-TZB-ALK	
Main Body	SWCH Trivalent Chromate Treatment (Silver)
Nylon Patch	Nylon 11



- Cross recessed head cap screws with extra low profile.
- With nylon patch.
- For space-saving of equipment/devices and applications with limited overhead space.
- QuaStix®¹ is used for the cross recess. By using a dedicated bit for QuaStix [SKQB], the torque transmission is improved, preventing cam-out and damage to the cross recess.*²
- The friction of the nylon adhered to the thread suppresses the return rotation of the thread.
- Even if the tightening force is lost, the return rotation is suppressed, preventing the screws from falling off.
- The heat resistant temperature of the nylon patch is 120°C.

*1: QuaStix is a registered trademark of OSG Corporation.

*2: It can be mounted and removed with ordinary Phillips bits.

● Application

Reducing the size of equipment and devices
Screw return and fallout prevented

Unit : mm

Part Number	M (Coarse) Nominal of Thread	Pitch	L				D ₁	L ₁	Bit Part No.	Max. Tightening Torque (N·m)* ¹	Mass (g)	Qty per Pack	
SEQ-M3-TZB-ALK	M3	0.5	6	8	10	12	7	0.8	SKQB-1	0.6	0.39 - 0.64	10	
SEQ-M4-TZB-ALK	M4	0.7		8	10	12	16	8	0.9	SKQB-2	1.2	0.8 - 1.4	10

*1: Values in chart are for reference only. They are not guaranteed values.

*2: When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Related Products

Use dedicated bit [SKQB] for mounting and removing.



● Part Number Specification

SEQ-M3-8-TZB-ALK**1** Individual Sales

Available / Add'l charge

2 Cleanroom Wash & Packaging

Available / Add'l charge

3 Screw Length Adjustment

Not Available

4 Vibration Resistant

Not Available

5 Modification process for captive use

Not Available