




SNZ-TZB Cross Recessed Micro Pan Head Screws - Type 0 - 1

Miniature Size



Material/Finish



	SNZ-TZB
Main Body	Steel Trivalent Chromate Treatment



- Miniature screws for precision instruments (No. 0 Class 1).
- M1 - M2.6.
- Pan head machine screw type with low head height. For applications with limited overhead space.
- Application

For making devices and equipment more compact
Compact precision equipment


Unit : mm

Part Number	M (Coarse)		L													D1	L1	Cross-recessed Socket No.	Max. Tightening Torque (N · m)	Mass (g)	Qty per Pack	
	Nominal of Thread	Pitch																				
SNZ-M1-TZB	M1	0.25				3	4									1.8	0.5	0	0.02	0.02	50	
SNZ-M1.2-TZB	M1.2	0.25		2	2.5	3		4	5							1.8	0.5	0	0.05	0.02 - 0.04	50	
SNZ-M1.4-TZB	M1.4	0.3	1.5	2	2.5	3	3.5	4	5	6	8	10	12			2	0.5	0	0.07	0.02 - 0.1	50	
SNZ-M1.6-TZB	M1.6	0.35	1.5	2	2.5	3	3.5	4	5	6	8	10	12			2.4	0.55	0	0.11	0.03 - 0.14	50	
SNZ-M1.7-TZB	M1.7	0.35	1.5	2	2.5	3	3.5	4	5	6	8	10	12	14		2.5	0.5	0	0.14	0.03 - 0.19	50	
SNZ-M2-TZB	M2	0.4	1.5	2	2.5	3	3.5	4	5	6	8	10	12	14	16	18	3	0.6	0	0.22	0.05 - 0.35	50
SNZ-M2.5-TZB	M2.5	0.45				3		4	5	6						3.8	0.9	0	0.46	0.14 - 0.22	50	
SNZ-M2.6-TZB	M2.6	0.45			2.5	3	3.5	4	5	6	8	10	12			4	0.8	0	0.53	0.14 - 0.43	50	

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

Part Number Specification

SNZ-M2-3-TZB



1 Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Available / Add'l charge	Not Available