




SNZF3-TBZ Cross Recessed Micro Flat Head Machine Screws - Type 0 - 3

🔍 Miniature Size



● Material/Finish

	SNZF3-TBZ	RoHS
Main Body	SWCH16A Black Trivalent Chromate Treatment	



- Miniature screws for precision instruments (Type 0 - 3).
- M1.4 - M2.6.
- Flat head machine screw type with low head height. For applications with limited overhead space.

● Application

For making devices and equipment more compact
Compact precision equipment

Part Number	M (Coarse)		L						D1	L1	Cross-recessed Socket No.	Max. Tightening Torque (N·m)*1	Mass (g)	Qty per Pack	Unit : mm	
	Nominal of Thread	Pitch	3	3.5	4	5	6	8								
SNZF3-M1.4-TBZ	M1.4	0.3	3	3.5	4	5	6		2.5	0.7	0		0.07		0.04 - 0.06	50
SNZF3-M1.7-TBZ	M1.7	0.35	3	3.5	4	5	6		3	0.8	0		0.14		0.06 - 0.09	50
SNZF3-M2-TBZ	M2	0.4	3	3.5	4	5	6	8	3.5	0.9	0		0.22		0.09 - 0.17	50
SNZF3-M2.6-TBZ	M2.6	0.45		3.5	4	5	6		4.5	1.1	0		0.53		0.18 - 0.25	50

*1 : Values in chart are for reference only. They are not guaranteed values.

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part Number Specification

SNZF3-M2-5-TBZ

1 2 1

1 Individual Sales Available / Add'l charge	2 Cleanroom Wash & Packaging Available / Add'l charge	3 Screw Length Adjustment Not Available	4 Vibration Resistant Available / Add'l charge	5 Modification process for captive use Not Available
--	--	--	---	---