



● Material/Finish



SNZF3-TZB

Main Body

SWCH16A

Trivalent Chromate Treatment



- Miniature screws for precision instruments (Type 0 - 3).
- M1.4 - M2.6.
- Flat head machine screw type with low head height. For applications with limited overhead space.

● Application

For making devices and equipment more compact
Compact precision equipment

Unit : mm

Part Number	M (Coarse)		L						D1	L1	Cross-recessed Socket No.	Max. Tightening Torque (N·m)*1	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch												
SNZF3-M1.4-TZB	M1.4	0.3	3	3.5	4	5	6		2.5	0.7	0	0.07	0.04 - 0.06	50
SNZF3-M1.7-TZB	M1.7	0.35	3	3.5	4		6		3	0.8	0	0.14	0.06 - 0.09	50
SNZF3-M2-TZB	M2	0.4		3.5	4	5	6	8	3.5	0.9	0	0.22	0.09 - 0.17	50
SNZF3-M2.6-TZB	M2.6	0.45		3.5	4	5	6		4.5	1.1	0	0.53	0.18 - 0.25	50

*1 : Values in chart are for reference only. They are not guaranteed values.

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part Number Specification

SNZF3-M2-5-TZB

Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Available / Add'l charge	Not Available