




SNZF-TZB

Cross Recessed Micro Flat Head Machine Screws - Type 0 - 1

Miniature Size



Material/Finish



	SNZF-TZB
Main Body	Steel Trivalent Chromate Treatment



- Miniature screws for precision instruments (Type 0 - 1).
- M1.4 - M2.6.
- Head is more compact than standard flat head machine screws.
- Application

For making devices and equipment more compact
Compact precision equipment

Unit : mm

Part Number	M (Coarse)		L										D ₁	L ₁	Cross-recessed Socket No.	Max. Tightening Torque (N・m)*1	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch	1.5	2	2.5	3	3.5	4	5	6	8	10						
SNZF-M1.4-TZB	M1.4	0.3	1.5	2	2.5	3	3.5	4	5	6	8	10	2.0	0.45	0	0.07	0.01 - 0.08	50
SNZF-M1.6-TZB	M1.6	0.35		2	2.5	3	3.5	4	5	6	8		2.4	0.5	0	0.11	0.03 - 0.09	50
SNZF-M1.7-TZB	M1.7	0.35		2	2.5	3	3.5	4	5	6	8	10	2.5	0.5	0	0.14	0.03 - 0.13	50
SNZF-M2-TZB	M2	0.4		2	2.5	3	3.5	4	5	6	8	10	3.0	0.6	0	0.22	0.04 - 0.18	50
SNZF-M2.5-TZB	M2.5	0.45				3		4	5	6			3.8	0.8	0	0.46	0.1 - 0.19	50
SNZF-M2.6-TZB	M2.6	0.45				3		4	5	6	8	10	4.0	0.8	0	0.53	0.12 - 0.33	50

*1: Values in chart are for reference only. They are not guaranteed values.

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

Part Number Specification

SNZF-M2-3-TZB



1 Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Available / Add'l charge	Not Available