




SNF-TBZ-SUC

Phillips Flat Head Screws for Sheet Metal

➡ Protrusion



● Material/Finish



SNF-TBZ-SUC

Main Body

SWCH12A


Black Trivalent Chromate Treatment




- Phillips flat head screws with cut seating surface.
- Suitable for sheet metal, preventing seating surface and incomplete threads from hitting the bottom when fixing sheet metal.

Standard flat head machine screw

SNF-TBZ-SUC



Incomplete thread part hits bottom



Cut seating surface prevents bottom hitting

- Incomplete thread part has no more than two peaks.
- Bolts for sheet metal are also available with special specifications such as dimensions, material, head shape, and so on. Please contact our customer service.

● Application

Reducing the size of equipment and devices

Unit : mm

Part Number	M (Coarse) Nominal of Thread	Pitch	L							D1	L1	Cross-recessed Socket No.	Mass (g)	Qty per Pack
SNF-M3-TBZ-SUC	M3	0.5	4	5	6	8	10			6	1.2	1	0.3 - 0.46	50
SNF-M4-TBZ-SUC	M4	0.7	4	5	6	8	10	12	15	8	1.5	2	0.3 - 1.2	50
SNF-M5-TBZ-SUC	M5	0.8		5	6	8	10	12	15	10	2	2	1.3 - 2.1	20
SNF-M6-TBZ-SUC	M6	1			6	8	10	12	15	12	2.3	2	1.7 - 3.4	20

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part Number Specification

SNF-M5-12-TBZ-SUC

1 Individual Sales

Available / Add'l charge

Cleanroom Wash & Packaging

Available / Add'l charge

Screw Length Adjustment

Not Available

Vibration Resistant

Available / Add'l charge

Modification process for captive use

Not Available