




SNFS-SUC Phillips Flat Head Screws for Sheet Metal

Protrusion SUS Stainless steel



● Material/Finish



SNFS-SUC

Main Body


SUSXM7 (Equivalent to SUS304)




- Stainless steel Phillips flat head screws with cut seating surface.
- Suitable for sheet metal, preventing seating surface and incomplete threads from hitting the bottom when fixing sheet metal.

Standard flat head machine screw

SNFS-SUC



Incomplete thread part hits bottom



Cut seating surface prevents bottom hitting

- Incomplete thread part has no more than two peaks.
- Bolts for sheet metal are also available with special specifications such as dimensions, material, head shape, and so on. Please contact our customer service.

● Application

Reducing the size of equipment and devices

Unit : mm

Part Number ①	M (Coarse)		L ②	D1	L1	Cross-recessed Socket No.	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch						
SNFS-M3-SUC	M3	0.5	4 5 6 8 10	6	1.2	1	0.32 - 0.42	50
SNFS-M4-SUC	M4	0.7	4 5 6 8 10 12	8	1.5	2	0.4 - 1.2	50
SNFS-M5-SUC	M5	0.8	5 6 8 10 12 15	10	2	2	1.7 - 3.2	20
SNFS-M6-SUC	M6	1	6 8 10 12 15 12	12	2.3	2	2.8 - 4.4	20

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part Number Specification

SNFS-M5-12-SUC

①

②

③

Individual Sales

Available / Add'l charge

Cleanroom Wash & Packaging

Available / Add'l charge

Screw Length Adjustment

Not Available

Vibration Resistant

Available / Add'l charge

Modification process for captive use

Not Available