




SPC-S Plastic Slotted Set Screws - PC

Lightweight Electrical Insulation



- PC (polycarbonate) slotted setscrews.
- PC (polycarbonate) has the highest shock resistance of engineering plastics.
- Allowable operating temperature*1 (min./max.): -40°C/115°C
- PC has low water absorbency and excellent weather resistance.
- For the properties and precautions for use of plastic screws, see "Properties of Plastic Screws."

• Application

Electrical and electronic equipment

• Material/Finish



	SPC-S
Main Body	PC (Polycarbonate) (Transparent)
Heat Resistance Temperature*1	115°C


*1 : This is the value for the resin material. The operating temperature of the product changes with performance conditions such as tightening torque.

Unit : mm

Part Number	M (Coarse)		L	a	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch				
SPC-M3-S	M3	0.5	4	0.8	0.07	50
SPC-M3-S(1000)	M3	0.5	4	0.8	0.07	1000
SPC-M4-S	M4	0.7	6	1.0	0.1	20
SPC-M4-S(1000)	M4	0.7	6	1.0	0.1	1000

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

• Part Number Specification



Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available