


NQTS-SPCR Spacers for Quick Release Fasteners

SUS Stainless steel



Material/Finish




	NQTS-SPCR
Main Body	SUS303
Hex Socket Countersunk Head Screw	Stainless Steel


- Spacer for mounting **NQTS** **NQTS-NI** **NQTS-F** **NQTS-F-NI** **NQTS-PH** **NQTS-PH-NI** to sheet metal.
- Made of stainless steel. It has excellent corrosion resistance.
- Two hex socket countersunk head screws for mounting are provided.

Part Number	D	d	E	S	Applicable Plate Thickness	Applicable Quick Clamp Fastener	Mass (g)
NQTS-5-SPCR	25	14	10	3	3~6	NQTS-5-BK NQTS-5-F-BK NQTS-5-NI NQTS-5-F-NI NQTS-6-PH-BK NQTS-6-PH-NI	9
NQTS-8-SPCR	34	18	13	3.5	3~6	NQTS-8-BK NQTS-8-F-BK NQTS-8-PH-BK NQTS-8-NI NQTS-8-F-NI NQTS-8-PH-NI	16


Usage Example



Mounting



Part Number	Applicable Plate Thickness	d	h	E	d1	d2
NQTS-5-SPCR	3	14	3	10	2.9	6
NQTS-8-SPCR	3	18	3	13	3.4	7.3



Part Number	Applicable Plate Thickness	d	D1	h	E	d1	d2
NQTS-5-SPCR	3~6	14	26	3	10	2.9	6
NQTS-8-SPCR	3~6	18	35	3	13	3.4	7.3

Part Number Specification

NQTS-5-SPCR



Cleanroom Wash & Packaging

Not Available

Laser Marking

Not Available