




SNB Socket Button Head Cap Screws



Material/Finish



	SNB
Main Body	SCM435 Ferrosoferric Oxide Film (Black)
Strength Class	10.9 or Higher

- Hex socket button head cap screws conforming to SSS Standard.

Unit : mm

Part Number 	M (Coarse)		L 																D ₁	L ₁	B	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch																					
SNB-M3	M3	0.5	5	6	8	10	12	16	20									5.5	2	2	0.47 - 1.1	20	
SNB-M4	M4	0.7		6	8	10	12	16	20	25	30							7.5	2.6	2.5	1.1 - 2.8	20	
SNB-M5	M5	0.8			8	10	12	16	20	25	30	35						9.5	3.4	3	2.3 - 5.3	20	
SNB-M6	M6	1				10	12	16	20	25	30	35	40					10.5	4	4	3.8 - 8.5	20	
SNB-M8	M8	1.25					12	16	20	25	30	35	40	45	50			14	5	5	8.1 - 19	10	
SNB-M10	M10	1.5						16	20	25	30	35	40	45	50			18	6	6	16 - 32	10	

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

Part Number Specification

SNB-M3-8


Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Not Available	Available / Add'l charge	Available / Add'l charge	Please feel free to contact us