

SNZF3S-ALK

Cross Recessed Micro Flat Head Machine Screws with Nylon Patch - Type 0-3




Vibration resistant treatment



Miniature Size



SUS Stainless steel



● Material/Finish

SNZF3S-ALK		
Main Body	Stainless Steel	
Nylon Patch	Nylon 11	



- Miniature screws with nylon patch for precision instruments (Type 0-3).
- M1.4 - M2.
- The friction of the nylon adhered to the thread suppresses the return rotation of the thread.
- Even if the tightening force is lost, the return rotation is suppressed, preventing the screws from falling off.
- The heat resistant temperature of the nylon patch is 120°C.
- Flat head machine screw type with low head height. For applications with limited overhead space.

● Application

Screw return and fallout prevented

For making devices and equipment more compact

Compact precision equipment

Part Number	M (Coarse)		L	D1	L1	Cross-recessed Socket No.	Max. Tightening Torque (N·m)*1	Mass (g)	Qty per Pack	Unit : mm
	Nominal of Thread	Pitch								
SNZF3S-M1.4-ALK	M1.4	0.3	3 3.5 4 5 6 8 10 2.5 0.7 0				0.03	0.04 - 0.09	50	
SNZF3S-M1.6-ALK	M1.6	0.35	3 4 5 6 8 10 2.8 0.8 0				0.05	0.05 - 0.12	50	
SNZF3S-M1.7-ALK	M1.7	0.35	3 3.5 4 5 6 8 10 3 0.8 0				0.07	0.04 - 0.13	50	
SNZF3S-M2-ALK	M2	0.4	3 4 5 6 8 10 3.5 0.9 0				0.12	0.09 - 0.21	50	

*1 : Values in chart are for reference only. They are not guaranteed values.

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part Number Specification

SNZF3S-M2-5-ALK**1** Individual Sales

Available / Add'l charge

2 Cleanroom Wash & Packaging

Available / Add'l charge

3 Screw Length Adjustment

Not Available

4 Vibration Resistant

Not Available

5 Modification process for captive use

Not Available