

- Dedicated cam base for mounting Quick Clamp Fasteners **NQTS-GL** **NQTS-NI-GL** **NQTS-F-GL** **NQTS-F-NI-GL**.
- The clamp part is tapered, making it easy to insert the Quick Clamp Fastener clamp pin.
- Made of stainless steel. It has excellent corrosion resistance.
- Uses low dust-emission grease.
- Two hex socket head cap screws for mounting are provided.

⚠ Precautions for Use
If the grease deteriorates or runs low, apply grease (THK Co., Ltd.'s AFF Grease) to the sliding part.

• Material/Finish




	NQTBS-GL
Main Body	Equivalent to SUS630
Hex Socket Head Cap Screw	Stainless Steel
Heat Resistance Temperature*1	100°C

*1: Upper limit temperature when using grease.

Part Number	H	L	D	t	B	R	Lc	E	Applicable Plate Thickness	Applicable Quick Clamp Fastener	Unit : mm	
											Mass (g)	
NQTBS-5-GL	25	9	14	4.5	5	3	3	10	10~	NQTS-5-GL NQTS-5-F-GL NQTS-5-NI-GL NQTS-5-F-NI-GL	18	
NQTBS-8-GL	32	10	20	5.5	8	3.5	3.5	13	12~	NQTS-8-GL NQTS-8-L-GL NQTS-8-F-GL NQTS-8-NI-GL NQTS-8-L-NI-GL NQTS-8-F-NI-GL	33	

- Mounting
Align the phase of the Quick Clamp Fastener **NQTS-GL** **NQTS-NI-GL** **NQTS-F-GL** **NQTS-F-NI-GL** clamp pin and the **NQTBS-GL** pin mounting hole for mounting.



Part Number	D	D1	h	E	Lf	M (Coarse)	
						Nominal of Thread	Pitch
NQTBS-5-GL	14	26	5	10	5	M2.5	0.45
NQTBS-8-GL	20	33	6	13	5	M3	0.5

Unit : mm

• Part Number Specification

NQTBS-8-GL

