




SWUS Hex Lock Nuts

Vibration resistant treatment **SUS** Stainless steel



- Nuts equipped with a high-performance mechanism of loosening prevention. Prevent loosening caused by vibration.
- Friction ring with very good restoration elasticity and heat resistance tighten the thread peak of the male thread from four sides. Effective for loosening prevention. The male thread is not damaged.
- Glass fiber reinforced polyamide is used for the friction ring. Rings with heat resistance effectively prevent loosening under conditions up to 110 °C. In addition, they are not affected by gasoline, alcohol, and oil.
- The friction ring retains most of its effects even after repeated use.

• Application


Vibration Resistant

• Material/Finish



SWUS	
Main Body	SUS304
Friction Ring	Glass Fiber Reinforced Polyamide

Unit : mm






Part Number 	M	B	C (Approx.)	T	Mass (g)	Qty per pack
SWUS-M6	M6	10	11.5	6	2	50
SWUS-M8	M8	13	15	8	4.6	20
SWUS-M10	M10	17	19.6	10	11	10
SWUS-M12	M12	19	21.9	12	16	10

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

• Part number specification

SWUS-M8



 Individual Sales → P.0000	 Cleanroom Wash & Packaging → P.0000	 Screw Length Adjustment → P.0000	 Vibration Resistant → P.0000	 Modification process for captive use → P.0000
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available