



● Material/Finish



	SJN Made of Steel	SJNS Made of Stainless Steel
Main body	SUM22L Ferrosferric Oxide Film (Black)	SUS303

Unit : mm

Part Number Steel	Part Number Stainless steel	M (Coarse)		L	Lf	B	Mass (g)
		Nominal of Thread	Pitch				
SJN-M2.5	SJNS-M2.5	M2.5	0.45	20	8	5	3
SJN-M3		M3	0.5	22	9	6	4
SJN-M4	SJNS-M4	M4	0.7	33	14	7	8
SJN-M6	SJNS-M6	M6	1	43	19	10	20
SJN-M8	SJNS-M8	M8	1.25	55	25	13	45
SJN-M10	SJNS-M10	M10	1.5	67	31	17	95
SJN-M12	SJNS-M12	M12	1.75	81	38	19	130
SJN-M16	SJNS-M16	M16	2	95	45	24	260
SJN-M20	SJNS-M20	M20	2.5	105	50	30	390

● Part number specification

SJN-M12



Cleanroom Wash & Packaging → P.xxxx	Screw Length Adjustment → P.xxxx	Vibration Resistant → P.xxxx	Laser Marking → P.xxxx
Please feel free to contact us	Not Available	Not Available	Please feel free to contact us