




Vibration resistant treatment



Tamper Resistance



SUS Stainless steel



### ● Material/Finish



	SRGFS-ALK
Main Body	SUSXM7
Nylon Patch	Nylon 11
Strength Class	Equivalent to A2-50

### ● Application

Equipment/devices disassembly/tampering prevention  
 Theft prevention for outdoor facilities  
 Security measures  
 Safety measures



- Five-lobe socket countersunk head screws with nylon patch.
- The friction of the nylon adhered to the thread suppresses the return rotation of the thread.
- Even if the tightening force is lost, the return rotation is suppressed, preventing the screws from falling off.
- The heat resistant temperature of the nylon patch is 120°C.
- This prevents mounting and removing with regular tools.
- Install and remove with **SRGB** Dedicated Bits and **SRD** Dedicated Magnetic Screwdriver together.

Unit : mm

Part Number	M (Coarse)		L								D1	L1	Bit Part No.	Screwdriver Part No.	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch														
SRGFS-M4-ALK	M4	0.7	10	16	20					8	2.3	SRGB-M4	SRD-6.35	1.03 - 1.78	10	
SRGFS-M5-ALK	M5	0.8	10	16	25	40				10	2.8	SRGB-M56	SRD-6.35	1.73 - 5.27	10	
SRGFS-M6-ALK	M6	1	12	16	20	30	40	50		12	3.4	SRGB-M56	SRD-6.35	3.04 - 9.63	10	

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

### ● Related Products

Washer for Flat Head Screw  
**SWAS-RW** is available.



**SRGB** applicable bits are available.



Dedicated magnetic screwdrivers **SRD** are available.



### ● Part Number Specification

**SRGFS-M5-16-ALK**

1

2

1

1 Individual Sales

Available / Add'l charge

Cleanroom Wash &amp; Packaging

Available / Add'l charge

Screw Length Adjustment

Not Available

Vibration Resistant

Not Available

Modification process for captive use

Not Available