




SRS6A System 6 Screws

Non-Magnetic

Lightweight

Tamper Resistance



Material/Finish



	SRS6A
Main Body	A5056



- Head has a special round shape with 6 grooves.
- Made of aluminum alloy. The specific gravity is approximately 33% that of stainless steel.
- There is no electrocorrosion due to contact with aluminum alloy.
- Corrosion resistance, electrical conductivity, and thermal conductivity are excellent.
- This prevents mounting and removing with regular tools, including pliers.
- Install and remove with **SKRS6K** Dedicated Bits and **SRD** Dedicated Magnetic Screwdriver.

Application

Equipment/devices disassembly/tampering prevention
Theft prevention for outdoor facilities
Security measures
Safety measures

Unit : mm

Part Number 1	M (Coarse)		L 2						D1	L1	Bit Part No.	Screwdriver Part No.	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch												
SRS6A-M3	M3	0.5	6	8	10				5.5	2.02	SKRS6K-3	SRD-6.35	0.15 - 0.21	10
SRS6A-M4	M4	0.7	6	8	10	12			7.5	2.5	SKRS6K-4	SRD-6.35	0.30 - 0.46	10
SRS6A-M5	M5	0.8		8	10	12	16		9.0	3.3	SKRS6K-5	SRD-6.35	0.63 - 0.93	10

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

Related Products

SKRS6K applicable bits are available.



Dedicated magnetic screwdrivers **SRD** are available.



Part Number Specification

SRS6A-M5-16



1 Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Not Available