


SWA-AW Adjusting Washers (Steel / Ferrosferic Oxide Film)



*D<20: C0.2 or less
D=20 or more: C0.5 or less

● Material/Finish

SWA-AW	
Main Body	Equivalent to S45C Ferrosferic Oxide Film (Black)



- There is a variety of outside diameters and thickness relative to normal plain washers.
- For securing seating surface on the long hole position and engagement of materials with low marginal seating surface pressure such as aluminum and resin.
- As a collar and a spacer, it can adjust the cumulative error in assembly.

● Application

Height adjustment / Seating surface fall prevention

Unit : mm

Part Number ¹	d	D	t ²					Mass (g)	Qty per Pack
			1	1.5	2	3	5		
SWA-2-8-AW	2	8	●		●			0.38 - 0.75	10
SWA-3-8-AW	3	8	●		●			0.35 - 0.69	10
SWA-3-10-AW	3	10	●		●			0.56 - 1.1	10
SWA-3-12-AW	3	12	●		●			0.83 - 1.7	10
SWA-3-15-AW	3	15	●		●			1.3 - 2.7	10
SWA-4-8-AW	4	8	●	●	●			0.3 - 0.6	10
SWA-4-10-AW	4	10	●		●	●		0.53 - 1.6	10
SWA-4-12-AW	4	12	●		●	●	●	0.8 - 3.9	10
SWA-4-15-AW	4	15	●		●	●	●	1.3 - 6.4	10
SWA-4-16-AW	4	16	●		●	●	●	1.5 - 7.4	10
SWA-4-18-AW	4	18	●		●	●	●	1.9 - 9.5	10
SWA-4-20-AW	4	20			●	●	●	4.7 - 12	10
SWA-4-25-AW	4	25			●	●	●	7.5 - 19	10
SWA-5-8-AW	5	8	●	●	●			0.25 - 0.49	10
SWA-5-10-AW	5	10	●		●	●		0.47 - 1.4	10
SWA-5-12-AW	5	12	●		●	●	●	0.74 - 3.7	10
SWA-5-15-AW	5	15	●		●	●	●	1.2 - 6.2	10
SWA-5-16-AW	5	16	●		●	●	●	1.4 - 7.1	10
SWA-5-18-AW	5	18	●		●	●	●	1.8 - 9.2	10
SWA-5-20-AW	5	20	●		●	●	●	2.3 - 12	10
SWA-5-25-AW	5	25			●	●	●	7.4 - 18	10

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

Unit : mm

Part Number ¹	d	D	t ²					Mass (g)	Qty per Pack
			1	1.5	2	3	5		
SWA-6-8-AW	6	8	●	●	●			0.17 - 0.34	10
SWA-6-10-AW	6	10	●		●	●		0.4 - 1.2	10
SWA-6-12-AW	6	12	●		●	●	●	0.68 - 3.3	10
SWA-6-15-AW	6	15	●		●	●	●	1.2 - 5.8	10
SWA-6-16-AW	6	16	●		●	●	●	1.4 - 6.8	10
SWA-6-18-AW	6	18	●		●	●	●	1.8 - 8.9	10
SWA-6-20-AW	6	20	●		●	●	●	2.3 - 11	10
SWA-6-25-AW	6	25	●		●	●	●	3.6 - 18	10
SWA-6-30-AW	6	30			●	●	●	11 - 27	10
SWA-8-12-AW	8	12	●		●	●	●	0.49 - 2.5	10
SWA-8-15-AW	8	15			●	●	●	2 - 5	10
SWA-8-16-AW	8	16			●	●	●	2.4 - 6	10
SWA-8-18-AW	8	18			●	●	●	3.2 - 8	10
SWA-8-20-AW	8	20			●	●	●	4.2 - 10	10
SWA-8-25-AW	8	25			●	●	●	7 - 17	10
SWA-8-30-AW	8	30			●	●	●	10 - 26	10
SWA-10-12-AW	10	12	●		●	●	●	0.27 - 1.4	10
SWA-10-15-AW	10	15			●	●	●	1.5 - 3.8	10
SWA-10-16-AW	10	16			●	●	●	1.9 - 4.8	10
SWA-10-18-AW	10	18			●	●	●	2.8 - 6.9	10
SWA-10-20-AW	10	20			●	●	●	3.7 - 9.3	10
SWA-10-25-AW	10	25				●	●	9.8 - 16	10
SWA-10-30-AW	10	30				●	●	15 - 25	10
SWA-10-35-AW	10	35				●	●	21 - 35	10
SWA-10-40-AW	10	40				●	●	28 - 46	10
SWA-10-50-AW	10	50				●	●	44 - 74	10
SWA-12-16-AW	12	16				●	●	2.1 - 3.5	10
SWA-12-18-AW	12	18				●	●	2.2 - 5.5	10
SWA-12-20-AW	12	20				●	●	3.2 - 8	10
SWA-12-25-AW	12	25				●	●	9 - 15	10
SWA-12-30-AW	12	30				●	●	14 - 23	10
SWA-12-35-AW	12	35				●	●	20 - 33	10
SWA-12-40-AW	12	40				●	●	27 - 45	10
SWA-12-50-AW	12	50				●	●	44 - 73	10
SWA-16-20-AW	16	20				●	●	1.8 - 4.5	10
SWA-16-25-AW	16	25				●	●	6.9 - 11	10
SWA-16-30-AW	16	30				●	●	12 - 20	10
SWA-16-35-AW	16	35				●	●	18 - 30	10
SWA-16-40-AW	16	40				●	●	25 - 41	10
SWA-16-50-AW	16	50				●	●	41 - 69	10
SWA-20-35-AW	20	35				●	●	15 - 25	10
SWA-20-40-AW	20	40				●	●	22 - 37	10
SWA-20-50-AW	20	50				●	●	39 - 65	10

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part Number Specification

SWA-2-8-1-AW



For ²t dimension, select from the sizes marked with ● in the table.

Individual Sales Available / Add'l charge	Cleanroom Wash & Packaging Not Available	Screw Length Adjustment Not Available	Vibration Resistant Not Available	Modification process for captive use Not Available
---	--	---------------------------------------	-----------------------------------	--