



#### Material/Finish



RoHS

	SNZB-ALK
Main Body	Brass*1
Nylon Patch	Nylon 11

\*1: The coloring may change over time or in response to environmental conditions, but the performance will not be affected.



- Miniature screws with nylon patch for precision instruments (Type 0 - 1).
- M2/M2.6.
- Pan head machine screw type with low head height. For applications with limited overhead space.
- Non-magnetic.
- The friction of the nylon adhered to the thread suppresses the return rotation of the thread.
- Even if the tightening force is lost, the return rotation is suppressed, preventing the screws from falling off.
- The heat resistant temperature of the nylon patch is 120°C.
- Application

For making devices and equipment more compact  
Screw return and fallout prevented  
FPD production equipment / Semiconductor manufacturing equipment / Electronic equipment / Miniature precision devices

Unit : mm

Part Number <span style="color: red;">◀1</span>	M (Coarse)		L <span style="color: red;">◀2</span>							D1	L1	Cross-recessed Socket No.	Max. Tightening Torque (N·m)*1	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch													
SNZB-M2-ALK	M2	0.4	3	4	5	6				3	0.6	0	0.09	0.08 - 0.14	20
SNZB-M2.6-ALK	M2.6	0.45		4	5		8	10		4	0.8	0	0.11	0.2 - 0.4	20

\*1: Values in chart are for reference only. They are not guaranteed values.

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

#### Part Number Specification

### SNZB-M2-3-ALK

◀1 ◀2 ◀1

Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available