

SNZ-TZB-ALK


Cross Recessed Micro Pan Head Screws with Nylon Patch - Type 0 - 1



Vibration resistant treatment



Miniature Size



● Material/Finish



RoHS

	SNZ-TZB-ALK
Main Body	Steel Trivalent Chromate Treatment
Nylon Patch	Nylon 11



- Miniature screws with nylon patch for precision instruments (No. 0 Class 1).
- M1 - M2.6.
- The friction of the nylon adhered to the thread suppresses the return rotation of the thread.
- Even if the tightening force is lost, the return rotation is suppressed, preventing the screws from falling off.
- The heat resistant temperature of the nylon patch is 120°C.
- Pan head machine screw type with low head height. For applications with limited overhead space.

● Application

Screw return and fallout prevented
For making devices and equipment more compact
Compact precision equipment

Unit : mm

Part Number 	M (Coarse)		L 												D1	L1	Cross-recessed Socket No.	Max. Tightening Torque (N · m)	Mass (g)	Qty per Pack	
	Nominal of Thread	Pitch																			
SNZ-M1-TZB-ALK	M1	0.25		3	4										1.8	0.5	0	0.01	0.02	50	
SNZ-M1.2-TZB-ALK	M1.2	0.25	2	2.5	3	4	5								1.8	0.5	0	0.03	0.02 - 0.04	50	
SNZ-M1.4-TZB-ALK	M1.4	0.3	2	2.5	3	3.5	4	5	6	8	10	12			2	0.5	0	0.05	0.02 - 0.1	50	
SNZ-M1.6-TZB-ALK	M1.6	0.35	2	2.5	3	3.5	4	5	6	8	10	12			2.4	0.55	0	0.07	0.03 - 0.14	50	
SNZ-M1.7-TZB-ALK	M1.7	0.35	2	2.5	3	3.5	4	5	6	8	10	12	14		2.5	0.5	0	0.09	0.04 - 0.19	50	
SNZ-M2-TZB-ALK	M2	0.4	2	2.5	3	3.5	4	5	6	8	10	12	14	16	18	3	0.6	0	0.18	0.06 - 0.35	50
SNZ-M2.5-TZB-ALK	M2.5	0.45		3	4	5	6								3.8	0.9	0	0.32	0.14 - 0.22	50	
SNZ-M2.6-TZB-ALK	M2.6	0.45	2	2.5	3	3.5	4	5	6	8	10	12			4	0.8	0	0.39	0.14 - 0.43	50	

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part Number Specification

SNZ-M2-3-TZB-ALK

1 Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available