

SNZ2-TBZ-ALK


Cross Recessed Micro Pan Head Screws with Nylon Patch - Type 0 - 2



Vibration resistant treatment



Miniature Size



● Material/Finish



RoHS

	SNZ2-TBZ-ALK
Main Body	Steel Black Trivalent Chromate Treatment
Nylon Patch	Nylon 11



- Miniature screws with nylon patch for precision instruments (No. 0 Class 2).
- M1.4 - M2.6.
- The friction of the nylon adhered to the thread suppresses the return rotation of the thread.
- Even if the tightening force is lost, the return rotation is suppressed, preventing the screws from falling off.
- The heat resistant temperature of the nylon patch is 120°C.
- Pan head machine screw type with low head height. For applications with limited overhead space.

● Application

Screw return and fallout prevented
For making devices and equipment more compact
Compact precision equipment

Unit : mm

Part Number 	M (Coarse)		L 	D1	L1	Cross-recessed Socket No.	Max. Tightening Torque (N·m)	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch							
SNZ2-M1.4-TBZ-ALK	M1.4	0.3	2 2.5 3 3.5 4 5 6 8 10	2.5	0.5	0	0.07	0.03 - 0.1	50
SNZ2-M1.6-TBZ-ALK	M1.6	0.35	2 2.5 3 3.5 4 5 6 8 10	2.8	0.55	0	0.11	0.04 - 0.12	50
SNZ2-M1.7-TBZ-ALK	M1.7	0.35	2 2.5 3 4 6 8 10	3.0	0.5	0	0.14	0.05 - 0.14	50
SNZ2-M2-TBZ-ALK	M2	0.4	2 2.5 3 3.5 4 5 6 8 10	3.5	0.6	0	0.22	0.07 - 0.21	50
SNZ2-M2.5-TBZ-ALK	M2.5	0.45	3 4 5 6 8 10	4.3	0.9	0	0.46	0.16 - 0.3	50
SNZ2-M2.6-TBZ-ALK	M2.6	0.45	2.5 3 3.5 4 5 6 8 10	4.5	0.8	0	0.53	0.16 - 0.39	50

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part Number Specification

SNZ2-M2-3-TBZ-ALK

 Individual Sales	 Cleanroom Wash & Packaging	 Screw Length Adjustment	 Vibration Resistant	 Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available