

SNZF3-TZB-ALK


Cross Recessed Micro Flat Head Machine Screws with Nylon Patch - Type 0 - 3



Vibration resistant treatment



Miniature Size



● Material/Finish



RoHS

	SNZF3-TZB-ALK
Main Body	SWCH16A Trivalent Chromate Treatment
Nylon Patch	Nylon 11



- Miniature screws with nylon patch for precision instruments (Type 0 - 3).
- M1.4 - M2.6.
- The friction of the nylon adhered to the thread suppresses the return rotation of the thread.
- Even if the tightening force is lost, the return rotation is suppressed, preventing the screws from falling off.
- The heat resistant temperature of the nylon patch is 120°C.
- Flat head machine screw type with low head height. For applications with limited overhead space.
- Application

Screw return and fallout prevented
For making devices and equipment more compact
Compact precision equipment

Unit : mm

Part Number	M (Coarse)		L						D1	L1	Cross-recessed Socket No.	Max. Tightening Torque (N·m)*1	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch												
SNZF3-M1.4-TZB-ALK	M1.4	0.3	3	3.5	4	5	6		2.5	0.7	0	0.05	0.04 - 0.06	50
SNZF3-M1.7-TZB-ALK	M1.7	0.35	3	3.5	4		6		3	0.8	0	0.09	0.06 - 0.09	50
SNZF3-M2-TZB-ALK	M2	0.4		3.5	4	5	6	8	3.5	0.9	0	0.18	0.09 - 0.17	50
SNZF3-M2.6-TZB-ALK	M2.6	0.45		3.5	4	5	6		4.5	1.1	0	0.39	0.18 - 0.25	50

*1 : Values in chart are for reference only. They are not guaranteed values.

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part Number Specification

SNZF3-M2-5-TZB-ALK

Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available