


**3V-4** ウェッジプーリー - 3V・3VX適用

単位: mm

品番	ピッチ径 dp	外径 de	最大軸穴径 d	下穴径 d	形状 図番	ハブ				リム		慣性モーメント (kg・m <sup>2</sup> )	質量 (kg)
						db	l	s1	s2	w	h <sup>+3</sup> <sub>0</sub>		
85-3V-4	83.8	86	35	-	11U	60	55	6.7	-	48.3	-	0.00135	1.82
90-3V-4	88.8	91	42	-	11U	76	55	6.7	-	48.3	-	0.00181	2.13
95-3V-4	93.8	96	42	-	11U	76	55	6.7	-	48.3	-	0.00226	2.38
100-3V-4	98.8	101	45	-	11U	76	55	6.7	-	48.3	-	0.00277	2.63
110-3V-4	108.8	111	50	-	11U	86	60	11.7	-	48.3	-	0.00439	3.46
112-3V-4	110.8	113	50	-	11U	86	60	11.7	-	48.3	-	0.0047	3.58
120-3V-4	118.8	121	50	-	11U	86	60	11.7	-	48.3	-	0.00614	4.07
125-3V-4	123.8	126	50	-	11U	86	60	11.7	-	48.3	-	0.00721	4.39
130-3V-4	128.8	131	50	-	11U	86	60	11.7	-	48.3	-	0.00843	4.73
140-3V-4	138.8	141	60	-	11U	100	70	21.7	-	48.3	-	0.0125	6.22
150-3V-4	148.8	151	60	-	11U	100	70	21.7	-	48.3	-	0.0162	7
160-3V-4	158.8	161	60	-	11U	100	70	21.7	-	48.3	-	0.0208	7.86
180-3V-4	178.8	181	55	-	10U	100	70	21.7	-	48.3	18	0.0238	7.34
200-3V-4	198.8	201	55	-	10U	100	70	21.7	-	48.3	18	0.0331	8.78
212-3V-4	210.8	213	60	-	10U	105	70	21.7	-	48.3	18	0.0409	8.91
224-3V-4	222.8	225	60	-	10U	105	70	21.7	-	48.3	18	0.0489	9.4
236-3V-4	234.8	237	60	-	10U	105	70	21.7	-	48.3	18	0.0581	9.92
250-3V-4	248.8	251	60	-	10Z	105	70	21.7	-	48.3	18	0.0682	10.2
280-3V-4	278.8	281	60	-	10Z	105	75	26.7	-	48.3	18	0.0999	11.7
300-3V-4	298.8	301	60	-	10Z	105	75	26.7	-	48.3	18	0.128	12.6
315-3V-4	313.8	316	60	-	10Z	105	75	26.7	-	48.3	18	0.152	13.4
355-3V-4	353.8	356	60	-	10Z	105	75	26.7	-	48.3	18	0.233	15.5
400-3V-4	398.8	401	60	-	10Z	105	75	26.7	-	48.3	18	0.35	17.5
450-3V-4	448.8	451	65	-	10Z	115	80	31.7	-	48.3	18	0.577	23.3
500-3V-4	498.8	501	65	-	10Z	115	80	31.7	-	48.3	18	0.914	29.1

**追加工サービスをご利用ください。**

Vプーリーに軸穴・キー溝・押しねじ穴の  
追加工をいたします。実働1日目出荷。



● 軸穴・キー溝・押しねじ追加工

対応可・別料金

**● 関連商品**

プーリーV溝部の摩耗を確認するためのゲージがあります。プーリーのメンテナンスの際に、ご利用ください。



● 品番指定 ※価格・納期はNBKウェブサイトをご覧ください。

**280-3V-4**